SPL785-50-5-PD

- **Fiber-Coupled Laser Diode**
- 785 nm, 50 mW
- 5 µm Single Mode Fiber
- **Built-in Photodiode**





Description

SPL785-50-5-PD is an infrared fiber-coupled laser diode, typically emitting at 785 nm with an output power of520 mW. It comes in a coaxial package with a mounting bracket, with 5 µm single mode fiber, FC/PC connector and built-in PD.

Additional options like alternative fiber connector or package are available on request.

Maximum Rating (TCASE = 25°C)

| Parameter | Cumbal | | l lmi4 | |
|---------------------------------|--------------|------|--------|------|
| rarameter | Symbol | Min. | Max. | Unit |
| Reverse Voltage | V_{R} | | 2.0 | V |
| PD Reverse Voltage | V_{PDR} | | 30 | V |
| Operating Temperature | T_{OPR} | - 10 | + 60 | °C |
| Storage Temperature | T STG | - 40 | + 85 | °C |
| Soldering Temperature (max. 3s) | T_{SOL} | | + 260 | °C |

Electro-Optical Characteristics (TCASE = 25°C)

| Parameter | | Symbol | Values | | | Unit |
|-----------------------|-------------|------------------|-------------|------|------|------|
| | | | Min. | Тур. | Max. | Unit |
| Peak Wavelength | | λ_{P} | 770 | 785 | 795 | nm |
| Output Power | | Po | | 50 | | mW |
| Spectral Width (FWHM) | | $\Delta \lambda$ | | | | nm |
| Threshold Current | | / th | | 30 | 50 | mA |
| Operating Current | | <i>I</i> F | | 120 | 140 | mA |
| Operating Voltage | | V_{F} | | 2.0 | 2.5 | V |
| PD Current | | <i>I</i> PD | | 0.3 | | mA |
| Fiber Specification | Type | | Single Mode | | | |
| | Core | | 5 | | | μm |
| | Connector * | | FC/PC | | | |
| | Length | | 80 | | | cm |


^{*} optional: SC or SMA905



www.roithner-laser.com


Electrical Connection

| Pin Configuration* | | | | | | |
|--------------------|----------------------|----|----|--|--|--|
| PIN# | Function | 10 | 03 | | | |
| 1 | LD Cathode | LD | PD | | | |
| 2 | LD Anode, PD Cathode | | | | | |
| 3 | PD Anode | | 02 | | | |





Outline Dimension



Optional: Coaxial Package

SPL785-50-C5-PD



All dimensions in mm

www.roithner-laser.com 2

^{*} subject to change

Precautions

Safety

Caution: Laser light emitted from any laser diode may be harmful to the human eye. Avoid looking directly into the laser diode's aperture when the diode is in operation.

Note: The use of optical lenses with this laser diode will increase eye hazard

ESD Caution

Always do handle laser diodes with extreme care to **prevent electrostatic discharge**, the primary cause of unexpected diode failure. To prevent ESD related failures we strongly advise to always **wearing wrist straps**, and **grounding all applicable work surfaces**, when handling laser diodes

STATIC SENSITIVE DEVICES HANDLE ONLY AT STATIC WORK STATIONS

ATTENTION

Operating Considerations

We strongly advise to only operate this laser diode with a current source. The current of a laser diode is an exponential function of the voltage across it. **Usage of current regulated drive circuits is mandatory**.

Laser diodes may be damaged by excessive drive currents or switching transients

It is advised, to operate the laser diode at the lowest temperature possible, and to never exceed maximum specifications as outlined in the datasheet. Device degradation will accelerate with increased temperature. Proper heat sinking will greatly enhance stability and life-time of the laser diode.

© All Rights Reserved

The above specifications are for reference purpose only and subjected to change without prior notice

www.roithner-laser.com 3